






Surface-mounted installation (Unit: mm)




Flush-mounted installation with pre-installation box (Unit: mm)




Installation height



Cavity wall installation (Unit: mm)




Preparation



Use gloves to protect yourself against cuts.


Surface-mounted installation

Option 1: on the wall




Mounting screw x 4  
Screw shaft:  $\varnothing 4$   
Screw length:  $\geq 25$  mm



Option 2: on the box (e.g. VDE box)




Mounting screw x 4  
Screw shaft:  $\varnothing 4$   
Screw length:  $\geq 25$  mm




Flush-mounted installation with pre-installation box




Mounting screw x 4  
Screw shaft:  $\varnothing 4$   
Screw length:  $\geq 25$  mm



## Cavity wall installation



Mounting screw x 4  
Screw shaft:  $\varnothing 4$   
Screw length:  $\geq 25$  mm



## Replace the nameplate

